

# 3M Fit Test Kit

## Product Images

---



## Description

---

The 3M Fit Test Kit allows for in-house testing of disposable, non-powered respirators. A sweet saccharin solution is sprayed at the subject while wearing their mask. If the subject is unable to test the solution, then the protection is adequate

- Designed to help organisation meet regulatory fit testing requirements for respirators
- Subject must be fully shaven for test to be accurate
- Can be used to check face-to-respirator seal on any particulate respirator or gas/vapour respirator with a particulate pre-filter
- Can be used with any negative pressure particulate respirator or gas and vapour respirator
- Initial fit-test is normally conducted when introducing new respiratory protective equipment
- CE Approved

Each Kit contains:

- 1 x hood and collar assembly
- 2 x nebulisers
- 1 x 55ml bottle of sensitivity solution
- 1 x 55ml bottle of test solution
- User instructions